



Generator bracket

Stat-X® bracket

Stat-X aerosol generators are listed for both sidewall and ceiling locations and may be mounted on walls, beams, constructions, and columns, as long as the unit is securely bolted to the support structure. Position the mounting bracket, and securely fasten it on a location and manner, which ensures the generator will not be subjected to accidental damage or movement. Securely attach a generator into the mounting bracket with generator clamps taking care to ensure the clamps are free of the initiator mechanism. The aerosol generator should be angled towards the floor at an angle to ensure three-



KG/18010



KG/18002



KG/18005



KG/18015

| Article code | Description | Diameter Ø | Weight | X dimension | Y dimension |
|-----------------|-------------------------|------------|----------|-------------|-------------|
| KG/18002 | Bracket 30/60SS | 2" / 51mm | 0,12 kg | 53 mm | 83 mm |
| KG/18005 | Bracket 100/250ME/250MT | 3" / 76mm | 0,27 kg | 102,4 mm | 103,1 mm |
| KG/18010 | Bracket 250/500/1000MT | 5" / 127mm | 0,562 kg | 158,8 mm | 185,4 mm |
| KG/18015 | Bracket 1000/1500/2500 | 8" / 203mm | 1,05 kg | 235,5 mm | 268,7 mm |

